


Compact air cylinder AEVUZ-25-15-P-A

Part number: 157223

FESTO



Data sheet

Feature	Value
Stroke	15 mm
Piston diameter	25 mm
Type code	AEVUZ
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position	Any
Mode of operation	Single-acting Pulling
Piston rod end	Internal thread
Structural design	Piston Piston rod
Position sensing	For proximity sensor
Symbol	00991204
Variants	Piston rod at one end
Operating pressure	1 bar ... 10 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Ambient temperature	-20 °C ... 80 °C
Impact energy in the end positions	0.1 J
Theoretical force at 6 bar, advancing	221 N
Moving mass at 0 mm stroke	26 g
Additional weight per 10 mm stroke	28 g
Basic weight with 0 mm stroke	180 g
Additional moving mass per 10 mm stroke	6 g
Type of mounting	Optionally: With through-hole With accessories
Pneumatic connection	M5
Flange screws material	Steel, galvanized
Cover material	Wrought aluminum alloy
Material of dynamic seals	NBR TPE-U(PU)
Piston rod material	High-alloy stainless steel
Material of cylinder barrel	Wrought aluminum alloy