


Servo motor EMMS-AS-140-LK-HS-RR

Part number: 1574662

FESTO



Data sheet

Feature	Value
Type code	EMMS-AS
Ambient temperature	-40 °C ... 40 °C
Storage temperature	-20 °C ... 60 °C
Relative air humidity	0 - 90 %
Conforms to standard	IEC 60034
Insulation protection class	F
Rating class according to EN 60034-1	S1
Temperature monitoring	PTC resistor
Degree of protection	IP54
Featherkey shaft design	DIN 6885 A 8 x 7 x 40
Electrical connection technology	Plug
Note on materials	RoHS-compliant
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS conformity	VDMA24364-B2-L
Certification	RCM compliance mark c UL us - Recognized (OL)
CE marking (see declaration of conformity)	As per EU EMC directive As per EU low voltage directive
DC nominal voltage	565 V
Type of winding switch	Star inside
Number of pole pairs	6
Stall torque	25.6 Nm
Nominal torque	21.12 Nm
Peak torque	48.8 Nm
Nominal rotary speed	2000 1/min
Max. rotational speed	2460 1/min
Motor nominal power	4420 W
Motor nominal current	7.8 A
Peak current	20 A
Motor constants	2.72 Nm/A
Voltage constant, phase-to-phase	162.39 mVmin
Phase-phase winding resistance	1.41 Ohm
Winding inductance phase-phase	13.44 mH
Total output inertia moment	18.4 kgcm ²
Product weight	16440 g

Feature	Value
Permissible axial shaft load	200 N
Permissible radial shaft load	1060 N
Rotor position sensor	Resolver
Rotor position sensor interface	SIN/COS analog signals
Rotor position sensor measuring principle	Inductive
MTTF, subcomponent	114 years, rotor position sensor
MTTFd, subcomponent	228 years, rotor position sensor
Energy efficiency	ENEFF (CN) / Class 2