



Compact air cylinder AEVUZ-12-5-A-P-A

Part number: 157252

FESTO



Data sheet

Feature	Value
Stroke	5 mm
Piston diameter	12 mm
Type code	AEVUZ
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position	Any
Mode of operation	Single-acting Pulling
Piston rod end	External thread
Structural design	Piston Piston rod
Position sensing	For proximity sensor
Symbol	00991204
Variants	Piston rod at one end
Operating pressure	1.5 bar ... 10 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Ambient temperature	-20 °C ... 80 °C
Impact energy in the end positions	0.07 J
Theoretical force at 6 bar, advancing	42 N
Moving mass at 0 mm stroke	8 g
Additional weight per 10 mm stroke	15 g
Basic weight with 0 mm stroke	87 g
Additional moving mass per 10 mm stroke	2 g
Type of mounting	Optionally: With through-hole With accessories
Pneumatic connection	M5
Flange screws material	High-alloy stainless steel
Cover material	Wrought aluminum alloy
Material of dynamic seals	NBR TPE-U(PU)
Piston rod material	High-alloy stainless steel
Material of cylinder barrel	Wrought aluminum alloy