


Servo motor EMMS-AS-190-MK-HS-AR-S1

Part number: 1584956

FESTO



Data sheet

Feature	Value
Type code	EMMS-AS
Ambient temperature	-10 °C ... 40 °C
Storage temperature	-20 °C ... 60 °C
Relative air humidity	0 - 90 %
Conforms to standard	IEC 60034
Insulation protection class	F
Rating class according to EN 60034-1	S1
Temperature monitoring	PTC resistor
Degree of protection	IP65
Featherkey shaft design	DIN 6885 A 10 x 8 x 40
Electrical connection technology	Plug
Note on materials	RoHS-compliant
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS conformity	VDMA24364-B2-L
Certification	RCM compliance mark c UL us - Recognized (OL)
CE marking (see declaration of conformity)	As per EU EMC directive As per EU low voltage directive
Nominal operating voltage DC	565 V
DC nominal voltage	565 V
Type of winding switch	Star inside
Number of pole pairs	6
Stall torque	38.77 Nm
Nominal torque	22.63 Nm
Peak torque	120 Nm
Nominal rotary speed	2900 1/min
Max. rotational speed	4060 1/min
Motor nominal power	6880 W
Motor nominal current	14.24 A
Peak current	88.2 A
Motor constants	1.589 Nm/A
Voltage constant, phase-to-phase	98.6 mVmin
Phase-phase winding resistance	0.265 Ohm
Winding inductance phase-phase	3.38 mH
Total output inertia moment	77 kgcm ²

Feature	Value
Product weight	27100 g
Permissible axial shaft load	250 N
Permissible radial shaft load	1080 N
Rotor position sensor	Resolver
Rotor position sensor interface	SIN/COS analog signals
Rotor position sensor measuring principle	Inductive
MTTF, subcomponent	114 years, rotor position sensor
MTTFd, subcomponent	228 years, rotor position sensor
Energy efficiency	ENEFF (CN) / Class 2