


# Flat cylinder DZF-40-160-P-A

Part number: 164060

FESTO



## Data sheet

| Feature                                      | Value                                                              |
|----------------------------------------------|--------------------------------------------------------------------|
| Stroke                                       | 160 mm                                                             |
| Piston diameter                              | 40 mm<br>Equivalent diameter                                       |
| Max. angle of rotation of the piston rod +/- | 0.6 deg                                                            |
| Type code                                    | DZF                                                                |
| Cushioning                                   | Elastic cushioning rings/pads at both ends                         |
| Mounting position                            | Any                                                                |
| Mode of operation                            | Double-acting                                                      |
| Structural design                            | Piston<br>Piston rod                                               |
| Position sensing                             | For proximity sensor                                               |
| Symbol                                       | 00991217                                                           |
| Protection against torsion/guide             | Oval piston                                                        |
| Operating pressure                           | 0.1 MPa ... 1 MPa                                                  |
| Operating pressure                           | 1 bar ... 10 bar                                                   |
| Operating medium                             | Compressed air as per ISO 8573-1:2010 [7:4:4]                      |
| Information on operating and pilot media     | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC)             | 2 - Moderate corrosion stress                                      |
| Ambient temperature                          | -20 °C ... 80 °C                                                   |
| Max. torque for protection against rotation  | 1 Nm                                                               |
| Theoretical force at 6 bar, retracting       | 633 N                                                              |
| Theoretical force at 6 bar, advancing        | 754 N                                                              |
| Moving mass at 0 mm stroke                   | 120 g                                                              |
| Additional weight per 10 mm stroke           | 40 g                                                               |
| Basic weight with 0 mm stroke                | 480 g                                                              |
| Additional moving mass per 10 mm stroke      | 16 g                                                               |
| Type of mounting                             | Optionally:<br>With internal thread<br>With accessories            |
| Pneumatic connection                         | G1/8                                                               |
| Cover material                               | Wrought aluminum alloy                                             |
| Seals material                               | NBR<br>TPE-U(PU)                                                   |
| Housing material                             | Aluminum<br>Smooth anodized                                        |
| Piston rod material                          | High-alloy steel                                                   |