



ISO cylinder DSBG-80-50-PPVA-N3

Part number: 1646773

FESTO



Data sheet

Feature	Value
Stroke	50 mm
Piston diameter	80 mm
Piston rod thread	M20x1.5
Type code	DSBG
Cushioning	Pneumatic cushioning, adjustable at both ends
Mounting position	Any
Conforms to standard	ISO 15552
Piston rod end	External thread
Structural design	Piston Piston rod Tie rod Cylinder barrel
Position sensing	For proximity sensor
Symbol	00991235
Variants	Piston rod at one end
Operating pressure	0.04 MPa ... 1.2 MPa
Operating pressure	0.4 bar ... 12 bar
Mode of operation	Double-acting
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Ambient temperature	-20 °C ... 80 °C
Impact energy in the end positions	1.8 J
Cushioning length	31 mm
Theoretical force at 6 bar, retracting	2721 N
Theoretical force at 6 bar, advancing	3016 N
Moving mass at 0 mm stroke	810 g
Additional weight per 10 mm stroke	85 g
Basic weight with 0 mm stroke	2660 g
Additional moving mass per 10 mm stroke	39 g
Type of mounting	Optionally: With internal thread With accessories
Pneumatic connection	G3/8
Note on materials	RoHS-compliant
Cover material	Die-cast aluminum, coated
Piston seal material	TPE-U(PU)

Feature	Value
Material of piston	Wrought aluminum alloy
Piston rod material	High-alloy steel
Piston rod wiper seal material	TPE-U(PU)
Buffer seal material	TPE-U(PU)
Cushion piston material	POM
Material of cylinder barrel	Wrought aluminum alloy, smooth-anodized
Nut material	Steel, galvanized
Material of bearing	POM
Collar nut material	Steel, galvanized
Tie rod material	High-alloy steel