

# ISO cylinder DSBG-100-25-PPSA-N3

Part number: 1646815

**FESTO**



## Data sheet

| Feature                                  | Value                                                              |
|------------------------------------------|--------------------------------------------------------------------|
| Stroke                                   | 25 mm                                                              |
| Piston diameter                          | 100 mm                                                             |
| Piston rod thread                        | M20x1.5                                                            |
| Type code                                | DSBG                                                               |
| Cushioning                               | Self-adjusting pneumatic end-position cushioning                   |
| Mounting position                        | Any                                                                |
| Conforms to standard                     | ISO 15552                                                          |
| Piston rod end                           | External thread                                                    |
| Structural design                        | Piston<br>Piston rod<br>Tie rod<br>Cylinder barrel                 |
| Position sensing                         | For proximity sensor                                               |
| Symbol                                   | 00992970                                                           |
| Variants                                 | Piston rod at one end                                              |
| Operating pressure                       | 0.04 MPa ... 1.2 MPa                                               |
| Operating pressure                       | 0.4 bar ... 12 bar                                                 |
| Mode of operation                        | Double-acting                                                      |
| Operating medium                         | Compressed air as per ISO 8573-1:2010 [7:4:4]                      |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC)         | 2 - Moderate corrosion stress                                      |
| Ambient temperature                      | -20 °C ... 80 °C                                                   |
| Impact energy in the end positions       | 2.5 J                                                              |
| Cushioning length                        | 31 mm                                                              |
| Theoretical force at 6 bar, retracting   | 4418 N                                                             |
| Theoretical force at 6 bar, advancing    | 4712 N                                                             |
| Moving mass at 0 mm stroke               | 1000 g                                                             |
| Additional weight per 10 mm stroke       | 94 g                                                               |
| Basic weight with 0 mm stroke            | 3665 g                                                             |
| Additional moving mass per 10 mm stroke  | 39 g                                                               |
| Type of mounting                         | Optionally:<br>With internal thread<br>With accessories            |
| Pneumatic connection                     | G1/2                                                               |
| Note on materials                        | RoHS-compliant                                                     |
| Cover material                           | Die-cast aluminum, coated                                          |
| Piston seal material                     | TPE-U(PU)                                                          |

| Feature                        | Value                                   |
|--------------------------------|-----------------------------------------|
| Material of piston             | Wrought aluminum alloy                  |
| Piston rod material            | High-alloy steel                        |
| Piston rod wiper seal material | TPE-U(PU)                               |
| Buffer seal material           | TPE-U(PU)                               |
| Cushion piston material        | POM                                     |
| Material of cylinder barrel    | Wrought aluminum alloy, smooth-anodized |
| Nut material                   | Steel, galvanized                       |
| Material of bearing            | POM                                     |
| Collar nut material            | Steel, galvanized                       |
| Tie rod material               | High-alloy steel                        |