


Ball valve VZBA-1"-GGG-63-32T-F0405-V4V4T

Part number: 1692227

FESTO



Data sheet

Feature	Value
Type code	VZBA
Structural design	3-way ball valve Drilled T hole
Actuation type	Mechanical
Sealing principle	Soft
Mounting position	Any
Type of mounting	Line installation
Fitting connection	Rp1
Switching position indication	Slot direction = flow direction
Flange hole pattern	F04 F05
Inside diameter	20 mm
Nominal width DN	25
Valve function	3/2
Manual override	None
Flow direction	Reversible
Nominal pressure of fitting PN	63
Actuating torque	22 Nm
Based on norm	EN 10226-1 ISO 5211
Symbol	00991888
Medium	Compressed air as per ISO 8573-1:2010 [-:--] Inert gas Water – no water vapor Neutral liquids Other flow media on request
Temperature of medium	-10 °C ... 200 °C
Flow rate Kv type T corner	10.9 m³/h
Flow rate Kv type T straight	22.4 m³/h
Note on materials	Contains paint-wetting impairment substances RoHS-compliant
Housing material	High-alloy stainless steel

Feature	Value
Material number of housing	1.4408
Seals material	PTFE PTFE-reinforced
Ball material	High-alloy stainless steel
Material number for ball	1.4408
Shaft material	High-alloy stainless steel
Material number for shaft	1.4401
Product weight	1600 g
Explosion prevention and protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Corrosion resistance class (CRC)	3 - High corrosion stress