


Guided actuator DFM-16-80-P-A-GF

Part number: 170838

FESTO



Data sheet

Feature	Value
Distance of centre of gravity of payload to yoke plate xs	50 mm
Stroke	80 mm
Piston diameter	16 mm
Type code	DFM
Drive unit operating mode	Yoke
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position	Any
Guide	Sliding guide
Structural design	Guide
Position sensing	For proximity sensor
Symbol	00991737
Operating pressure	0.2 MPa ... 1 MPa
Operating pressure	2 bar ... 10 bar
Max. speed	0.8 m/s
Mode of operation	Double-acting
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-20 °C ... 80 °C
Impact energy in the end positions	0.15 J
Max. permissible torque load Mx as a function of the stroke	1.28 Nm
Max. payload as a function of the stroke at defined distance xs	55 N
Theoretical force at 6 bar, retracting	90 N
Theoretical force at 6 bar, advancing	121 N
Moving mass	428 g
Product weight	960 g
Alternative connections	See product drawing
Pneumatic connection	M5
Note on materials	RoHS-compliant
Cover material	Wrought aluminum alloy
Seals material	NBR
Housing material	Wrought aluminum alloy
Piston rod material	High-alloy stainless steel