



# Motor cable NEBM-M40G8-E-10-Q10N-LE8

Part number: 1750242

FESTO



## Data sheet

Feature	Value
Type code	NEBM
Cable designation	Without label holder
Electrical connection 1, function	Field device end
Electrical connection 1, design	Round
Electrical connection 1, connection type	Socket
Electrical connection 1, cable outlet	Straight
Electrical connection 1, connection technology	M40x1.5
Electrical connection 1, number of pins/wires	8
Electrical connection 1, occupied pins/wires	8
Electrical connection for input 1, connection pattern	00995662
Electrical connection 2, function	Control side
Electrical connection 2, connection type	Cable
Electrical connection 2, connection technology	Open end
Electrical connection 2, number of pins/wires	8
Electrical connection 2, occupied pins/wires	8
DC operating voltage range	0 V ... 630 V
Note on operating voltage range DC	0 - 300 V for conductor cross-section of 0.75 mm <sup>2</sup>
Operating voltage range AC	0 V ... 630 V
Note on operating voltage range AC	0 - 300 V for conductor cross-section of 0.75 mm <sup>2</sup>
Current rating at 40°C	22 A
Note on acceptable current load at 40°C	12 A for conductor cross-section of 0.75 mm <sup>2</sup>
Surge resistance	4 kV
Note on surge resistance	2.5 kV for a conductor cross-section of 0.75 mm <sup>2</sup>
Cable length	10 m
Cable characteristic	Suitable for energy chains
Bending radius, fixed cable installation	≥70 mm
Bending radius, flexible cable installation	≥140 mm
Cable diameter	14 mm
Cable design	4 x 2.5 mm <sup>2</sup> + 2 x (2 x 0.75 mm <sup>2</sup> ) Shielded
Nominal conductor cross section	2.5 mm <sup>2</sup> 0.75 mm <sup>2</sup>
Wire ends	Cable end sleeve
Degree of protection	IP65

<b>Feature</b>	<b>Value</b>
Note on degree of protection	In mounted state
Ambient temperature	-50 °C ... 90 °C
Ambient temperature with flexible cable installation	-40 °C ... 90 °C
CE marking (see declaration of conformity)	As per EU low voltage directive As per EU RoHS directive
Note on materials	RoHS-compliant
Contamination level	3
Corrosion resistance class (CRC)	0 - No corrosion stress
Material of cable sheath	TPE-U(PUR)
Color cable sheath	Orange
Insulating sheath material	TPE-E