


# Guided actuator DFM-12-25-P-A-KF

Part number: 170901

FESTO



## Data sheet

| Feature                                                         | Value                                                              |
|-----------------------------------------------------------------|--------------------------------------------------------------------|
| Distance of centre of gravity of payload to yoke plate xs       | 25 mm                                                              |
| Stroke                                                          | 25 mm                                                              |
| Piston diameter                                                 | 12 mm                                                              |
| Type code                                                       | DFM                                                                |
| Drive unit operating mode                                       | Yoke                                                               |
| Cushioning                                                      | Elastic cushioning rings/pads at both ends                         |
| Mounting position                                               | Any                                                                |
| Guide                                                           | Recirculating ball bearing guide                                   |
| Structural design                                               | Guide                                                              |
| Position sensing                                                | For proximity sensor                                               |
| Symbol                                                          | 00991737                                                           |
| Operating pressure                                              | 0.2 MPa ... 1 MPa                                                  |
| Operating pressure                                              | 2 bar ... 10 bar                                                   |
| Max. speed                                                      | 0.8 m/s                                                            |
| Mode of operation                                               | Double-acting                                                      |
| Operating medium                                                | Compressed air as per ISO 8573-1:2010 [7:4:4]                      |
| Information on operating and pilot media                        | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC)                                | 0 - No corrosion stress                                            |
| Ambient temperature                                             | -5 °C ... 60 °C                                                    |
| Impact energy in the end positions                              | 0.07 J                                                             |
| Max. force Fy                                                   | 193 N                                                              |
| Max. force Fy static                                            | 355 N                                                              |
| Max. force Fz                                                   | 193 N                                                              |
| Max. force Fz static                                            | 355 N                                                              |
| Max. torque Mx                                                  | 3.95 Nm                                                            |
| Max. static moment Mx                                           | 7.28 Nm                                                            |
| Max. torque My                                                  | 1.74 Nm                                                            |
| Max. static moment My                                           | 3.2 Nm                                                             |
| Max. torque Mz                                                  | 1.74 Nm                                                            |
| Max. static moment Mz                                           | 3.2 Nm                                                             |
| Max. permissible torque load Mx as a function of the stroke     | 0.66 Nm                                                            |
| Max. payload as a function of the stroke at defined distance xs | 23 N                                                               |
| Theoretical force at 6 bar, retracting                          | 51 N                                                               |
| Theoretical force at 6 bar, advancing                           | 68 N                                                               |
| Moving mass                                                     | 170 g                                                              |
| Product weight                                                  | 375 g                                                              |

| Feature                                                          | Value                                     |
|------------------------------------------------------------------|-------------------------------------------|
| Center of gravity of the moving mass as a function of the stroke | 16.7 mm                                   |
| Alternative connections                                          | See product drawing                       |
| Pneumatic connection                                             | M5                                        |
| Note on materials                                                | Free of copper and PTFE<br>RoHS-compliant |
| Cover material                                                   | Wrought aluminum alloy                    |
| Seals material                                                   | NBR                                       |
| Housing material                                                 | Wrought aluminum alloy                    |
| Piston rod material                                              | High-alloy stainless steel                |