


Guided actuator DFM-16-30-P-A-KF

Part number: 170910

FESTO



Data sheet

Feature	Value
Distance of centre of gravity of payload to yoke plate xs	50 mm
Stroke	30 mm
Piston diameter	16 mm
Type code	DFM
Drive unit operating mode	Yoke
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position	Any
Guide	Recirculating ball bearing guide
Structural design	Guide
Position sensing	For proximity sensor
Symbol	00991737
Operating pressure	0.2 MPa ... 1 MPa
Operating pressure	2 bar ... 10 bar
Max. speed	0.8 m/s
Mode of operation	Double-acting
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	0 - No corrosion stress
Ambient temperature	-5 °C ... 60 °C
Impact energy in the end positions	0.15 J
Max. force Fy	389 N
Max. force Fy static	415 N
Max. force Fz	389 N
Max. force Fz static	415 N
Max. torque Mx	8.95 Nm
Max. static moment Mx	9.55 Nm
Max. torque My	3.89 Nm
Max. static moment My	4.15 Nm
Max. torque Mz	3.89 Nm
Max. static moment Mz	4.15 Nm
Max. permissible torque load Mx as a function of the stroke	1.52 Nm
Max. payload as a function of the stroke at defined distance xs	37 N
Theoretical force at 6 bar, retracting	90 N
Theoretical force at 6 bar, advancing	121 N
Moving mass	249 g
Product weight	537 g

Feature	Value
Center of gravity of the moving mass as a function of the stroke	20.8 mm
Alternative connections	See product drawing
Pneumatic connection	M5
Note on materials	Free of copper and PTFE RoHS-compliant
Cover material	Wrought aluminum alloy
Seals material	NBR
Housing material	Wrought aluminum alloy
Piston rod material	High-alloy stainless steel