

Parallel gripper HGPP-20-A-G1

Part number: 187874

FESTO



Data sheet

Feature	Value
Size	20
Stroke per gripper jaw	7.5 mm
Max. interchangeability	0.1 mm
Pneumatic gripper repetition accuracy	≤0.02 mm
Type code	HGPP
Number of gripper jaws	2
Mode of operation	Double-acting
Gripper function	Parallel
Gripping force backup	On opening
Structural design	Gear rack/pinion
Position sensing	For Hall sensor For inductive proximity sensors
Symbol	00995947
Operating pressure	5 bar ... 8 bar
Max. operating frequency of pneumatic gripper	4 Hz
Min. opening time at 6 bar	45 ms
Min. closing time at 6 bar	92 ms
Max. mass per external gripper finger	200 g
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Ambient temperature	5 °C ... 60 °C
Maximum force on gripper jaw Fz, static	220 N
Maximum torque on gripper jaw, Mx static	14 Nm
Maximum torque on gripper jaw, My static	14 Nm
Maximum torque on gripper jaw, Mz static	14 Nm
Product weight	611 g
Type of mounting	With internal thread
Pneumatic connection	M5
Note on materials	Free of copper and PTFE
Cover cap material	POM
Housing material	Wrought aluminum alloy Hard-anodized
Gripper jaw material	Wrought aluminum alloy Nickel-plated