


Mini guided actuator DFC-6-30-P-A-KF

Part number: 189466

FESTO



Data sheet

Feature	Value
Distance of centre of gravity of payload to yoke plate xs	10 mm
Stroke	30 mm
Piston diameter	6 mm
Type code	DFC
Drive unit operating mode	Yoke
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position	Any
Guide	Recirculating ball bearing guide
Structural design	Guide
Position sensing	For proximity sensor
Symbol	00991737
Operating pressure	1.5 bar ... 10 bar
Max. speed	1 m/s
Mode of operation	Double-acting
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	0 - No corrosion stress
Ambient temperature	-5 °C ... 60 °C
Impact energy in the end positions	0.008 J
Max. torque Mx	0.1 Nm
Max. payload as a function of the stroke at defined distance xs	4.6 N
Theoretical force at 6 bar, retracting	12.5 N
Theoretical force at 6 bar, advancing	17 N
Moving mass	8.8 g
Moving mass at 0 mm stroke	8.8 g
Product weight	55 g
Additional moving mass per 10 mm stroke	2.8 g
Pneumatic connection	M3
Cover material	Wrought aluminum alloy
Seals material	NBR
Housing material	Wrought aluminum alloy
Piston rod material	High-alloy stainless steel