


# Ball valve actuator unit VZBA-1/4"-GGG-63-32L-F0304-V4V4T-PP30-R-90-C

Part number: 1914785

**FESTO**



## Data sheet

| Feature                                  | Value                                                                                                  |
|------------------------------------------|--------------------------------------------------------------------------------------------------------|
| Type code                                | VZBA                                                                                                   |
| Structural design                        | 3-way ball valve<br>Drilled L hole                                                                     |
| Actuation type                           | Pneumatic                                                                                              |
| Mounting position                        | Any                                                                                                    |
| Type of mounting                         | Line installation                                                                                      |
| Fitting connection                       | Rp1/4                                                                                                  |
| Switching position indication            | Slot direction = flow direction                                                                        |
| Nominal width DN                         | 8                                                                                                      |
| Operating pressure                       | 6 bar ... 8.4 bar                                                                                      |
| Nominal pressure of fitting PN           | 63                                                                                                     |
| Symbol                                   | 00995329                                                                                               |
| Medium                                   | Compressed air as per ISO 8573-1:2010 [:-:-]<br>Inert gas<br>Water – no water vapor<br>Neutral liquids |
| Operating medium                         | Compressed air as per ISO 8573-1:2010 [7:4:4]                                                          |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use)                                     |
| Temperature of medium                    | -10 °C ... 200 °C                                                                                      |
| Ambient temperature                      | -10 °C ... 80 °C                                                                                       |
| Flow rate Kv type L                      | 4.5 m³/h                                                                                               |
| Max. surface temperature of assembly     | TX                                                                                                     |
| Explosion group of assembly              | IIC, IIIC                                                                                              |
| Note on materials                        | Contains paint-wetting impairment substances<br>RoHS-compliant                                         |
| Housing material                         | High-alloy stainless steel                                                                             |
| Material number of housing               | 1.4408                                                                                                 |
| Seals material                           | PTFE<br>PTFE-reinforced                                                                                |
| Ball material                            | High-alloy stainless steel                                                                             |
| Material number for ball                 | 1.4408                                                                                                 |
| Shaft material                           | High-alloy stainless steel                                                                             |
| Material number for shaft                | 1.4401                                                                                                 |
| Product weight                           | 1750 g                                                                                                 |
| Explosion prevention and protection      | Zone 1 (ATEX)<br>Zone 2 (ATEX)<br>Zone 21 (ATEX)<br>Zone 22 (ATEX)                                     |

| Feature                          | Value                     |
|----------------------------------|---------------------------|
| Explosive ambient temperature    | -10°C ≤ Ta ≤ +60°C        |
| Corrosion resistance class (CRC) | 3 - High corrosion stress |