

ISO cylinder DSNU-16-150-PPS-A

Part number: 1908281

FESTO



Data sheet

Feature	Value
Stroke	150 mm
Piston diameter	16 mm
Piston rod thread	M6
Type code	DSNU
Cushioning	Self-adjusting pneumatic end-position cushioning
Mounting position	Any
Conforms to standard	CETOP RP 52 P ISO 6432
Piston rod end	External thread
Structural design	Piston Piston rod Cylinder barrel
Position sensing	For proximity sensor
Variants	Piston rod at one end
Operating pressure	0.1 MPa ... 1 MPa
Operating pressure	1 bar ... 10 bar
Mode of operation	Double-acting
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Ambient temperature	-20 °C ... 80 °C
Impact energy in the end positions	0.15 J
Cushioning length	12 mm
Theoretical force at 6 bar, retracting	103.7 N
Theoretical force at 6 bar, advancing	120.6 N
Moving mass at 0 mm stroke	23 g
Additional weight per 10 mm stroke	4.6 g
Basic weight with 0 mm stroke	89.9 g
Additional moving mass per 10 mm stroke	2 g
Type of mounting	With accessories
Pneumatic connection	M5
Note on materials	RoHS-compliant
Cover material	Wrought aluminum alloy Plain anodized
Seals material	NBR TPE-U(PU)
Piston rod material	High-alloy stainless steel

Feature	Value
Material of cylinder barrel	High-alloy stainless steel