


# Shut off valve HEP-1/2-D-MIDI

Part number: 193252

**FESTO**



## Data sheet

| Feature                                  | Value                                                              |
|------------------------------------------|--------------------------------------------------------------------|
| Type code                                | HEP                                                                |
| Structural design                        | Piston gate valve                                                  |
| Actuation type                           | Pneumatic                                                          |
| Sealing principle                        | Soft                                                               |
| Exhaust air function                     | Without flow control option                                        |
| Manual override                          | None                                                               |
| Reset method                             | Mechanical spring                                                  |
| Symbol                                   | 00991173                                                           |
| Valve function                           | 3/2, closed, monostable                                            |
| Operating pressure                       | 0 bar ... 16 bar                                                   |
| Pilot pressure                           | 3 bar ... 16 bar                                                   |
| C value                                  | 16.6 l/sbar                                                        |
| b-value                                  | 0.4                                                                |
| Standard nominal flow rate               | 3900 l/min                                                         |
| Operating medium                         | Compressed air as per ISO 8573-1:2010 [7:4:4]<br>Inert gas         |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC)         | 2 - Moderate corrosion stress                                      |
| Note on materials                        | RoHS-compliant                                                     |
| Temperature of medium                    | -10 °C ... 60 °C                                                   |
| Ambient temperature                      | -10 °C ... 60 °C                                                   |
| Type of mounting                         | Line installation<br>With accessories                              |
| Mounting position                        | Any                                                                |
| Flow direction                           | Non-reversible                                                     |
| Product weight                           | 500 g                                                              |
| Pneumatic connection 1                   | G1/2                                                               |
| Pneumatic connection 2                   | G1/2                                                               |
| Pneumatic connection 3                   | G1/4                                                               |
| Pilot air port 12                        | G1/8                                                               |
| Air quality class at the output          | Compressed air as per ISO 8573-1:2010 [7:4:4]<br>Inert gas         |
| Seals material                           | NBR                                                                |
| Housing material                         | Die-cast aluminum                                                  |