


# Vacuum generator VN-07-L-T3-PQ2-VQ2-R01

Part number: 193572

FESTO



## Data sheet

| Feature                                       | Value   |
|---|---|
| Nominal width of Laval nozzle                 | 0.7 mm  |
| Width dimension                               | 14 mm   |
| Type code                                     | VN  |
| Muffler construction type                     | Open  |
| Mounting position                             | Any   |
| Ejector characteristics                       | High suction rate<br>Standard                 |
| Integrated function                           | Pneumatic muffler open                        |
| Structural design                             | T-shape                                       |
| Symbol  | 00991489                                      |
| Operating pressure for max. suction rate      | 6.2 bar                                       |
| Operating pressure                            | 1 bar ... 8 bar                               |
| Nominal operating pressure                    | 6 bar   |
| Max. suction rate with respect to atmosphere  | 38.8 l/min                                    |
| Air supply time at nominal operating pressure | 0.5 s   |
| Operating medium                              | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media      | Operation with oil lubrication not possible   |
| Corrosion resistance class (CRC)              | 1 - Low corrosion stress                      |
| Temperature of medium                         | 0 °C ... 60 °C                                |
| Noise level at nominal operating pressure     | 66 dB(A)                                      |
| Ambient temperature                           | 0 °C ... 60 °C                                |
| Max. tightening torque                        | 0.5 Nm  |
| Product weight                                | 24 g  |
| Type of mounting                              | With through-hole<br>With accessories         |
| Pneumatic connection 1                        | QS-6  |
| Pneumatic connection 3                        | Pneumatic muffler open                        |
| Vacuum connection                             | QS-6  |
| Material of connecting thread                 | Brass, nickel-plated                          |
| Note on materials                             | Free of copper and PTFE<br>RoHS-compliant     |
| Seals material                                | NBR   |
| Female nozzle material                        | POM   |
| Housing material                              | POM-reinforced                                |
| Muffler material                              | PE  |
| Material of jet nozzle                        | Wrought aluminum alloy                        |

| Feature                       | Value                  |
|-------------------------------|------------------------|
| Material of pneumatic fitting | Brass<br>Nickel-plated |