


# Air preparation unit FRCS-1/2-D-5M-MAXI

Part number: 194944

**FESTO**



## Data sheet

| Feature                                  | Value                                                                             |
|------------------------------------------|-----------------------------------------------------------------------------------|
| Size                                     | Maxi                                                                              |
| Type code                                | FRCS                                                                              |
| Series                                   | D                                                                                 |
| Actuator lock                            | Rotary knob with integrated lock                                                  |
| Mounting position                        | Vertical +/- 5°                                                                   |
| Condensate drain                         | Manually rotating                                                                 |
| Structural design                        | Filter regulator with pressure gauge<br>Proportional standard oil mist lubricator |
| Max. condensate volume                   | 80 ml                                                                             |
| Grade of filtration                      | 5 µm                                                                              |
| Bowl guard                               | Metal bowl guard                                                                  |
| Symbol                                   | 00991761                                                                          |
| Pressure gauge                           | with pressure gauge                                                               |
| Operating pressure                       | 1 bar ... 16 bar                                                                  |
| Pressure regulation range                | 0.5 bar ... 12 bar                                                                |
| Max. pressure hysteresis                 | 0.4 bar                                                                           |
| Standard nominal flow rate               | 6800 l/min                                                                        |
| Operating medium                         | Compressed air as per ISO 8573-1:2010 [-:9:-]<br>Inert gas                        |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use)                |
| Air quality class at the output          | Compressed air as per ISO 8573-1:2010 [6:8:-]<br>Inert gas                        |
| Temperature of medium                    | -10 °C ... 60 °C                                                                  |
| Ambient temperature                      | -10 °C ... 60 °C                                                                  |
| Product weight                           | 2490 g                                                                            |
| Type of mounting                         | Line installation<br>With accessories                                             |
| Pneumatic connection 1                   | G1/2                                                                              |
| Pneumatic connection 2                   | G1/2                                                                              |
| Note on materials                        | RoHS-compliant                                                                    |
| Housing material                         | Die-cast zinc                                                                     |
| Material of bowl                         | PC                                                                                |