


# Round cylinder ESNU-63-50-P

Part number: 195881

FESTO



## Data sheet

Feature	Value
Stroke	50 mm
Piston diameter	63 mm
Piston rod thread	M16x1.5
Type code	ESNU
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position	Any
Structural design	Piston Piston rod Cylinder barrel
Symbol	00991730
Operating pressure	0.12 MPa ... 1 MPa
Operating pressure	1.2 bar ... 10 bar
Mode of operation	Single-acting Pushing
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Ambient temperature	-20 °C ... 80 °C
Spring resetting force with piston rod in retracted position	60 N
Theoretical force at 6 bar, retracting	60 N
Theoretical force at 6 bar, advancing	1763 N
Moving mass	584 g
Moving mass at 0 mm stroke	459 g
Additional weight per 10 mm stroke	44 g
Basic weight with 0 mm stroke	1445 g
Product weight	1665 g
Additional moving mass per 10 mm stroke	25 g
Type of mounting	With accessories
Pneumatic connection	G3/8
Note on materials	RoHS-compliant
Cover material	Wrought aluminum alloy
Seals material	NBR TPE-U(PU)
Piston rod material	High-alloy steel
Material of cylinder barrel	High-alloy stainless steel