



Air solenoid valve

MHA1-M5H-2/2G-0,9-TC

FESTO

Part number: 197040



Data sheet

Feature	Value
Valve function	2/2, closed, monostable
Actuation type	Electrical
Width	10 mm
Standard nominal flow rate	14 l/min
Pneumatic working port	Sub-base
Operating voltage	12V DC
Operating pressure	-0.9 bar ... 2 bar
Structural design	Poppet valve with return spring
Reset method	Mechanical spring
Degree of protection	IP40
Certification	c UL us - Recognized (OL)
Certificate issuing authority	UL MH19482
Nominal width	0.9 mm
Width dimension	10 mm
Type code	MHA1
Exhaust air function	Without flow control option
Sealing principle	Soft
Mounting position	Any
Manual override	Non-detenting
Type of control	Direct
Flow direction	Non-reversible
Symbol	00991398
Valve position ID	Label
Lap	Underlap
Note on forced dynamization	Switching frequency at least once a week
Suitability for vacuum	yes
Max. switching frequency	20 Hz
Switching time off	5 ms
On switching time	4 ms
Duty cycle	100%
Electrical power consumption	1 W
Coil characteristics	12 V DC: 1.0 W
Permissible voltage fluctuations	+/- 10 %
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)

Feature	Value
Vibration resistance	Transport application test with severity level 2 as per FN 942017-4 and EN 60068-2-6
Shock resistance	Shock test with severity level 2 as per FN 942017-5 and EN 60068-2-27
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Storage temperature	-20 °C ... 60 °C
Temperature of medium	-5 °C ... 40 °C
Ambient temperature	-5 °C ... 40 °C
Product weight	10 g
Electrical connection	Plug
Type of mounting	On sub-base With through-hole
Pneumatic connection 1	Sub-base
Pneumatic connection 2	Sub-base
Note on materials	Free of copper and PTFE RoHS-compliant
Seals material	FPM HNBR NBR
Housing material	PA-reinforced PPS-reinforced