


Round cylinder DSNU-63-200-P-A

Part number: 196017

FESTO



Data sheet

| Feature | Value |
|--|--|
| Stroke | 200 mm |
| Piston diameter | 63 mm |
| Piston rod thread | M16x1.5 |
| Type code | DSNU |
| Cushioning | Elastic cushioning rings/pads at both ends |
| Mounting position | Any |
| Structural design | Piston Piston rod Cylinder barrel |
| Position sensing | For proximity sensor |
| Symbol | 00991217 |
| Operating pressure | 0.1 MPa ... 1 MPa |
| Operating pressure | 1 bar ... 10 bar |
| Mode of operation | Double-acting |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| Ambient temperature | -20 °C ... 80 °C |
| Theoretical force at 6 bar, retracting | 1681.9 N |
| Theoretical force at 6 bar, advancing | 1870.3 N |
| Moving mass | 959 g |
| Product weight | 2325 g |
| Type of mounting | With accessories |
| Pneumatic connection | G3/8 |
| Note on materials | RoHS-compliant |
| Cover material | Wrought aluminum alloy |
| Seals material | NBR TPE-U(PU) |
| Piston rod material | High-alloy steel |
| Material of cylinder barrel | High-alloy stainless steel |