



Parallel gripper HGPL-40-20-A-B

Part number: 3361487

FESTO



Data sheet

Feature	Value
Size	40
Stroke per gripper jaw	20 mm
Max. interchangeability	<0.2 mm
Max. gripper jaw angular play ax, ay	<0.2 deg
Max. gripper jaw backlash Sz	<0.05 mm
Rotational symmetry	≤0.2 mm
Pneumatic gripper repetition accuracy	<0.03 mm
Type code	HGPL
Number of gripper jaws	2
Mounting position	Any
Mode of operation	Double-acting
Gripper function	Parallel
Structural design	Twin piston Guide Piston gate valve T-shape Gear rack/pinion
Position sensing	For proximity sensor
Symbol	00991894
Total gripping force at 6 bar, opening	1038 N
Total gripping force at 6 bar, closing	1216 N
Operating pressure	3 bar ... 8 bar
Max. operating frequency of pneumatic gripper	<1 Hz
Min. opening time at 6 bar	190 ms
Min. closing time at 6 bar	180 ms
Max. mass per external gripper finger	420 g
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Ambient temperature	5 °C ... 60 °C
Gripping force per gripper jaw at 6 bar, opening	519 N
Gripping force per gripper jaw at 6 bar, closing	608 N
Mass moment of inertia	27.6 kgcm ²
Maximum force on gripper jaw Fz, static	2500 N
Maximum torque on gripper jaw, Mx static	125 Nm
Maximum torque on gripper jaw, My static	80 Nm
Maximum torque on gripper jaw, Mz static	100 Nm

Feature	Value
Relubrication interval for guidance elements	5 MioCyc
Product weight	2560 g
Type of mounting	With internal thread and centering sleeve Via through-hole and centering sleeve
Pneumatic connection	M5
Note on materials	Free of copper and PTFE RoHS-compliant
Housing material	Aluminum Smooth anodized
Gripper jaw material	Steel Hardened