

Rotary actuator ERMO-12-ST-E

Part number: 3008525

FESTO



Data sheet

Feature	Value
Size	12
Type code	ERMO
Structural design	Electromechanical rotary actuator with integrated gearbox
Mounting position	Any
Type of mounting	With internal thread
Rotation angle	Infinite
Gear ratio	9:1
Nominal torque	0.15 Nm
Nominal rotary speed	100 1/min
Max. rotational speed	200 1/min
Torsional backlash	0.2 deg
Repetition accuracy	±0.05 °
Max. axial force	180 N
Max. radial force	200 N
Permissible mass moment of inertia	3.0E-4 kgm ²
Product weight	475 g
Step angle with full step	1.8 deg
Step angle tolerance	±5%
Mass moment of inertia JO	0.0079 kgcm ²
Duty cycle	100%
Nominal operating voltage DC	24 V
Motor nominal current	0.8 A
Insulation protection class	B
Motor type	Stepper motor
Rotor position sensor	Incremental encoder
Rotor position sensor interface	RS422 TTL A/B channels + zero index
Rotor position sensor measuring principle	Optical
Electrical connection technology	Plug
CE marking (see declaration of conformity)	As per EU EMC directive
Bending radius, fixed cable installation	≥60 mm
Interface code, base	E8-35
Degree of protection	IP40
Ambient temperature	0 °C ... 50 °C
Relative air humidity	0 - 85 % Non-condensing

Feature	Value
Note on materials	Contains paint-wetting impairment substances RoHS-compliant
Material of flange	Wrought aluminum alloy Anodized
Housing material	Wrought aluminum alloy Anodized