

# Ball screw linear actuator EGC-70-400-BS-10P-KF-0H-ML-GK

FESTO

Part number: 3013391



## Data sheet

Feature	Value
Working stroke	400 mm
Size	70
Stroke reserve	0 mm
Screw diameter	12 mm
Spindle pitch	10 mm/U
Type code	EGC
Mounting position	Any
Guide	Recirculating ball bearing guide
Structural design	Electromechanical linear axis with ball screw
Motor type	Stepper motor Servo motor
Spindle type	Ball screw
Symbol	00991211
Max. acceleration	15 m/s <sup>2</sup>
Max. speed	0.5 m/s ... 0.75 m/s
Repetition accuracy	±0.02 mm
Duty cycle	100%
Degree of protection	IP40
Ambient temperature	-10 °C ... 60 °C
2nd moment of area Ix	419000 mm <sup>4</sup>
2nd moment of area Iy	578000 mm <sup>4</sup>
2nd moment of area Iz	419000 mm <sup>4</sup>
Max. force Fy	1850 N
Max. force Fz	1850 N
Max. torque Mx	16 Nm
Max. radial force on actuator shaft	220 N
Max. feed force Fx	400 N
Torsion moment of inertia It	88000 mm <sup>4</sup>
Mass moment of inertia JH per meter of stroke	0.142 kgcm <sup>2</sup>
Feed constant	10 mm/U
Material of end caps	Wrought aluminum alloy Anodized
Moment compensator material	Wrought aluminum alloy Anodized
Profile material	Wrought aluminum alloy Anodized

<b>Feature</b>	<b>Value</b>
Note on materials	RoHS-compliant
Drive cover material	Wrought aluminum alloy Anodized
Slide carriage material	Steel
Guide rail material	Steel
Slide material	Wrought aluminum alloy Anodized
Spindle nut material	Steel
Spindle material	Steel