

Sensor box SRBG-C1-N-1-AS-M12-M12

Part number: 3567908

FESTO



Data sheet

Feature	Value
Type code	SRBG
Design	Rectangular
Based on norm	EN 60947-5-2 VDI/VDE 3845
Certification	RCM compliance mark c UL us (OL)
CE marking (see declaration of conformity)	As per EU EMC directive
KC characters	KC EMC
Note on materials	Contains paint-wetting impairment substances RoHS-compliant
Measuring principle	Inductive
Ambient temperature	-25 °C ... 70 °C
Switching output	AS-Interface
Switching element function	N/C contact/N/O contact switchable
Max. switching frequency	100 Hz
Max. switching output voltage DC	26.4 V
Max. output current DC	100 mA
Max. switching capacity DC	2.5 W
Protocol	AS-Interface
AS-Interface, protocol version	V3.0
AS-Interface, addressing range	1A ... 31A (0) 1B ... 31B
AS-Interface, product identification	I/O code: D ID code: A ID1 code: 7 ID2 code: E
DC operating voltage range	26.5 V ... 31.6 V
Idle current	≤35 mA
Electrical connection, input	Plug M12x1 4-pin
Electrical connection, output	Socket M12x1 4-pin
Mounting position	Any
Product weight	70 g
Housing material	PBT
Material of screws	High-alloy stainless steel
Ready status indication	LED green

Feature	Value
Switching status indication	LED yellow
Status indicator	LED yellow = pneumatic valve switching status LED red = wire break/short circuit at pneumatic valve
Storage temperature	-25 °C ... 70 °C
Degree of protection	IP67
Shock resistance	Shock test with severity level 2 as per FN 942017-5 and EN 60068-2-27
Vibration resistance	Transport application test with severity level 2 as per FN 942017-4 and EN 60068-2-6
Contamination level	3