

Servo motor EMME-AS-80-M-HS-AMX

Part number: 4267592

FESTO



Data sheet

Feature	Value
Type code	EMME-AS
Ambient temperature	-10 °C ... 40 °C
Storage temperature	-20 °C ... 70 °C
Relative air humidity	0 - 90 %
Conforms to standard	IEC 60034
Insulation protection class	F
Rating class according to EN 60034-1	S1
Degree of protection	IP21
Electrical connection technology	Plug
Note on materials	RoHS-compliant
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS conformity	VDMA24364 zone III
Certification	RCM compliance mark c UL us - Recognized (OL)
CE marking (see declaration of conformity)	As per EU EMC directive As per EU low voltage directive
Nominal operating voltage DC	565 V
DC nominal voltage	565 V
Type of winding switch	Star inside
Number of pole pairs	3
Stall torque	3.5 Nm
Nominal torque	3.2 Nm
Peak torque	14 Nm
Nominal rotary speed	3000 1/min
Max. rotational speed	4097 1/min
Motor nominal power	1000 W
Continuous stall current	2.2 A
Motor nominal current	2.1 A
Peak current	8.8 A
Motor constants	1.524 Nm/A
Voltage constant, phase-to-phase	97.5 mVmin
Phase-phase winding resistance	9 Ohm
Winding inductance phase-phase	22.8 mH
Total output inertia moment	1.93 kgcm ²
Product weight	3700 g
Permissible axial shaft load	72 N

Feature	Value
Permissible radial shaft load	360 N
Rotor position sensor	Safety encoder, absolute multi-turn
Rotor position sensor interface	HIPERFACE®
Rotor position sensor measuring principle	Optical
Rotor position encoder, sinusoidal/cosinusoidal periods per revolution	128
Typical rotor position sensor resolution	15 bit
Rotor position encoder, typical angular accuracy	20 arcmin
Safety Integrity Level (SIL), subcomponent	SIL 2, rotor position sensor SILCL 2, rotor position sensor
Performance Level (PL), subcomponent	Category 3, performance level d, rotor position encoder
PFHd, subcomponent	1.3 x 10E-8, rotor position sensor
Duration of use Tm, subcomponent	20 years, rotor position sensor
MTTFd, subcomponent	874 years, rotor position sensor
Energy efficiency	ENEFF (CN) / Class 2