


Filter regulator LFR-1/2-D-16-O-MIDI-T18-EX4

Part number: 4772771

FESTO



Data sheet

| Feature | Value |
|--|--|
| Size | Midi |
| Type code | LFR |
| Series | D |
| Actuator lock | Rotary knob with detent |
| Mounting position | Vertical +/- 5° |
| Grade of filtration | 40 µm |
| Condensate drain | Manually rotating |
| Structural design | Filter regulator without pressure gauge |
| Max. condensate volume | 42 ml |
| Bowl guard | Integrated as metal bowl guard |
| Symbol | 00991586 |
| Pressure gauge | G1/4 prepared |
| Operating pressure | 0.1 MPa ... 2 MPa |
| Operating pressure | 1 bar ... 20 bar |
| Pressure regulation range | 0.5 bar ... 16 bar |
| Max. pressure hysteresis | 0.2 bar |
| Standard nominal flow rate | 1970 l/min |
| CE marking (see declaration of conformity) | as per EU explosion protection directive (ATEX) |
| Explosion prevention and protection | Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX) |
| ATEX category gas | II 2G |
| ATEX category for dust | II 2D |
| Type of ignition protection for gas | Ex h IIC T6 Gb X |
| Type of (ignition) protection for dust | Ex h IIIC T85°C Db X |
| Explosive ambient temperature | -20°C ≤ Ta ≤ +80°C |
| Operating medium | Compressed air as per ISO 8573-1:2010 [-:9:-] Inert gas |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 3 - High corrosion stress |
| Storage temperature | -20 °C ... 80 °C |
| Air quality class at the output | Compressed air as per ISO 8573-1:2010 [7:8:4] Inert gas |
| Temperature of medium | -20 °C ... 80 °C |
| Ambient temperature | -20 °C ... 80 °C |
| Product weight | 1400 g |

| Feature | Value |
|------------------------|--|
| Type of mounting | Optionally: Line installation With accessories |
| Pneumatic connection 1 | G1/2 |
| Pneumatic connection 2 | G1/2 |
| Note on materials | RoHS-compliant |
| Housing material | Die-cast zinc |
| Material of bowl | Wrought aluminum alloy |