


Compact air cylinder DPDM-10-10-P-PA

Part number: 4832171

FESTO



Data sheet

Feature	Value
Stroke	10 mm
Piston diameter	10 mm
Type code	DPDM
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position	Any
Mode of operation	Single-acting Pulling
Structural design	Piston Piston rod Profile barrel
Position sensing	For proximity sensor
Symbol	00991850
Variants	Piston rod at one end
Operating pressure	0.2 MPa ... 0.8 MPa
Operating pressure	2 bar ... 8 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-10 °C ... 80 °C
Theoretical force at 6 bar, retracting	31 N
Theoretical force at 6 bar, advancing	31 N
Moving mass at 0 mm stroke	7 g
Additional weight per 10 mm stroke	7.5 g
Basic weight with 0 mm stroke	30 g
Additional moving mass per 10 mm stroke	1 g
Type of mounting	Optionally: With through-hole With internal thread
Pneumatic connection	M5
Note on materials	RoHS-compliant
Cover material	Wrought aluminum alloy
Seals material	TPE-U(PU)
Housing material	Wrought aluminum alloy, anodized
Piston rod material	High-alloy stainless steel