


# Plug socket with cable SIM-M12-8GD-15-PU

Part number: 5105631

FESTO



## Data sheet

Feature	Value
Type code	SIM
Conforms to standard	DIN 47100 EN 61076-2-101
Cable designation	Without label holder
Electrical connection 1, function	Field device end
Electrical connection 1, design	Round
Electrical connection 1, connection type	Socket
Electrical connection 1, cable outlet	Straight
Electrical connection 1, connection technology	M12x1 A-coded as per EN 61076-2-101
Electrical connection 1, number of pins/wires	8
Electrical connection 1, occupied pins/wires	8
Electrical connection 1, type of mounting	Screw-type lock
Electrical connection for input 1, connection pattern	00992265
Electrical connection 2, function	Control side
Electrical connection 2, connection type	Cable
Electrical connection 2, connection technology	Open end
Electrical connection 2, number of pins/wires	8
Electrical connection 2, occupied pins/wires	8
DC operating voltage range	0 V ... 30 V
Operating voltage range AC	0 V ... 30 V
Current rating at 40°C	2 A
Surge resistance	0.8 kV
Cable length	15 m
Cable characteristic	Standard
Bending radius, fixed cable installation	≥32 mm
Bending radius, flexible cable installation	≥66 mm
Cable diameter	6.3 mm
Cable diameter tolerance	± 0.2 mm
Cable design	8 x 0.25 mm <sup>2</sup> Shielded
Nominal conductor cross section	0.25 mm <sup>2</sup>
Wire ends	Tin-plated
Degree of protection	IP67
Note on degree of protection	In mounted state

<b>Feature</b>	<b>Value</b>
Ambient temperature	-25 °C ... 85 °C
Ambient temperature with flexible cable installation	-5 °C ... 80 °C
CE marking (see declaration of conformity)	As per EU EMC directive
Note on materials	RoHS-compliant
Contamination level	3
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Material of cable sheath	TPE-U(PUR)
Color cable sheath	Gray
Housing material	TPE-U(PUR)
Material of screw-type lock	Brass, nickel-plated
Material of pin contacts	Bronze, gold-plated
Insulating sheath material	PP