



Motor cable NEBM-M23G15-EH-7.5-Q9N-R3LEG14

Part number: 5251383

FESTO



Data sheet

Feature	Value
Type code	NEBM
Based on norm	EN 61984
Cable designation	Without label holder
Product weight	2850 g
Electrical connection 1, function	Field device end
Electrical connection 1, design	Round
Electrical connection 1, connection type	Hybrid socket
Electrical connection 1, cable outlet	Straight
Electrical connection 1, connection technology	M23x1
Electrical connection 1, number of pins/wires	15
Electrical connection 1, occupied pins/wires	12
Electrical connection 1, type of mounting	Screw-type lock
Electrical connection for input 1, connection pattern	00995912
Electrical connection 2, function	Control side
Electrical connection 2, connection type	Plugs and cables
Electrical connection 2, cable outlet	Straight
Electrical connection 2, connection technology	RJ45 and open end
Electrical connection 2, number of pins/wires	14
Electrical connection 2, occupied pins/wires	12
DC operating voltage range	0 V ... 850 V
Operating voltage range AC	0 V ... 630 V
Current rating at 40°C	17.8 A
Surge resistance	6 kV
Cable length	7.5 m
Cable characteristic	Suitable for energy chains
Connector cable test conditions	Test conditions on request
Bending radius, fixed cable installation	≥51.2 mm
Bending radius, flexible cable installation	≥96 mm
Cable diameter	12.8 mm
Cable diameter tolerance	± 0.3 mm
Cable design	4 x 1.5 mm ² + 1 x (2 x 0.75 mm ²) + 1 x (2 x 0.24 mm ²) + 2 x 2 x 0.15 mm ² Shielded

Feature	Value
Nominal conductor cross section	1.5 mm ² 0.75 mm ² 0.15 mm ² 0.24 mm ²
Wire ends	Cable end sleeve
Degree of protection	IP67
Note on degree of protection	In mounted state
Ambient temperature	-40 °C ... 90 °C
Ambient temperature with flexible cable installation	-25 °C ... 80 °C
CE marking (see declaration of conformity)	As per EU low voltage directive
Note on materials	RoHS-compliant Halogen-free
Contamination level	3
Corrosion resistance class (CRC)	1 - Low corrosion stress
Material of cable sheath	TPE-U(PUR)
Color cable sheath	Gray
Insulating sheath material	PP