


Connecting cable KM12-8GD8GS-2-PU

Part number: 525617

FESTO



Data sheet

Feature	Value
Type code	KM12
Cable designation	Without label holder
Contact durability	50
Product weight	140 g
Electrical connection 1, function	Field device end
Electrical connection 1, design	Round
Electrical connection 1, connection type	Socket
Electrical connection 1, cable outlet	Straight
Electrical connection 1, connection technology	M12x1 A-coded as per EN 61076-2-101
Electrical connection 1, number of pins/wires	8
Electrical connection 1, occupied pins/wires	8
Electrical connection 1, type of mounting	Screw-type lock
Electrical connection for input 1, connection pattern	00992265
Electrical connection 2, function	Control side
Electrical connection 2, design	Round
Electrical connection 2, connection type	Plug
Electrical connection 2, cable outlet	Straight
Electrical connection 2, connection technology	M12x1 A-coded as per EN 61076-2-101
Electrical connection 2, number of pins/wires	8
Electrical connection 2, occupied pins/wires	8
Electrical connection 2, type of mounting	Screw-type lock
Electrical connection 2, connection pattern	00992264
DC operating voltage range	0 V ... 30 V
Nominal operating voltage DC	30 V
Operating voltage range AC	0 V ... 30 V
Current rating at 40°C	2 A
Surge resistance	0.8 kV
Cable length	2 m
Cable characteristic	Standard
Connector cable test conditions	Test conditions on request
Bending radius, fixed cable installation	≥32 mm
Bending radius, flexible cable installation	≥64 mm
Cable diameter	6.2 mm
Cable diameter tolerance	± 0.2 mm

Feature	Value
Cable design	8 x 0.25 mm ² Shielded
Nominal conductor cross section	0.25 mm ²
Degree of protection	IP67
Note on degree of protection	In mounted state
Ambient temperature	-25 °C ... 80 °C
Ambient temperature with flexible cable installation	0 °C ... 80 °C
CE marking (see declaration of conformity)	As per EU RoHS directive
Note on materials	RoHS-compliant
Contamination level	3
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Material of cable sheath	TPE-U(PUR)
Color cable sheath	Gray
Material of screw-type lock	Brass, chrome-plated Brass, nickel-plated
Seals material	NBR
Material of pin contacts	Brass, nickel-plated and gold-plated
Insulating sheath material	PP TPE-U(PUR)