


Pressure gauge kit DPA-63-16-MA-SET

Part number: 526097

FESTO



Data sheet

Feature	Value
Type code	DPA
Symbol	00991463
Conforms to standard	EN 837-1
Pressure gauge nominal size	40
Structural design	Bourdon tube pressure gauge
Type of mounting	With external thread
Operating pressure	16 bar
Measurement accuracy class	2.5
Degree of protection	IP43
Ambient temperature	5 °C ... 60 °C
Note on materials	RoHS-compliant
Mounting position	Any
Pneumatic connection	G1/8
Product weight	250 g