


Compact air cylinder AEN-S-10-5-I-A

Part number: 5269268

FESTO



Data sheet

Feature	Value
Stroke	5 mm
Piston diameter	10 mm
Type code	AEN-S
Cushioning	No cushioning
Mounting position	Any
Mode of operation	Pushing
Piston rod end	Internal thread
Structural design	Piston Piston rod
Position sensing	For proximity sensor
Symbol	00991201
Variants	Piston rod at one end
Operating pressure	0.15 MPa ... 0.8 MPa
Operating pressure	1.5 bar ... 8 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-10 °C ... 60 °C
Impact energy in the end positions	0.012 J
Theoretical force at 6 bar, retracting	5.3 N
Theoretical force at 6 bar, advancing	41.7 N
Moving mass	4.5 g
Product weight	17 g
Type of mounting	With through-hole
Pneumatic connection	M3
Note on materials	RoHS-compliant
Cover material	Wrought aluminum alloy
Material of dynamic seals	NBR TPE-U(PU)
Housing material	Wrought aluminum alloy Anodized
Piston rod material	High-alloy stainless steel