


Air line lubricator LOE-M7-D-MICRO-B

Part number: 534188

FESTO



Data sheet

| Feature | Value |
|-------------------------------------------|--------------------------------------------------------------------|
| Size | Micro |
| Type code | LOE |
| Series | D |
| Mounting position | Vertical +/- 5° |
| Structural design | Proportional standard oil mist lubricator |
| Max. oil capacity | 6.5 cm ³ |
| Symbol | 00991532 |
| Operating pressure | 1 bar ... 10 bar |
| Minimum flow rate for lubricator function | 3 l/min |
| Standard nominal flow rate | 430 l/min |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] Inert gas |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| Storage temperature | -10 °C ... 60 °C |
| Air quality class at the output | Compressed air as per ISO 8573-1:2010 [7:4:-] Inert gas |
| Temperature of medium | -10 °C ... 60 °C |
| Oil viscosity | ISO VG 32 |
| Ambient temperature | -10 °C ... 60 °C |
| Product weight | 39 g |
| Type of mounting | Optionally: Line installation With accessories |
| Pneumatic connection 1 | M7 |
| Pneumatic connection 2 | M7 |
| Note on materials | RoHS-compliant |
| Housing material | Wrought aluminum alloy |
| Material of bowl | PC |