


# Pick and place machine HSW-10-AS-SD

Part number: 540227

FESTO



## Data sheet

Feature	Value
Working stroke	9 mm ... 15 mm
Size	10
Max. linear stroke at 90° swivel angle	90/90 mm
Z-stroke	80 mm ... 100 mm
Type code	HSW
Cushioning	Acoustic insulation via buffers
Mounting position	Any
Structural design	Actuator shaft Linear guide plus ball bearing Positively driven motion sequence
Position sensing	For proximity sensor
Repetition accuracy end positions	+/-0.02 mm
Ambient temperature	0 °C ... 60 °C
Max. driving torque on actuator shaft	0.85 Nm
Max. axial force at actuator shaft	10 N
Max. torque Mx	0.6 Nm
Max. torque My	0.6 Nm
Max. torque Mz	0.6 Nm
Max. payload	0.5 kg
Max. radial force on actuator shaft	30 N
Maximum process force in y direction	30 N
Product weight	1300 g
Type of mounting	Via through-hole and centering sleeve
Note on materials	Free of copper and PTFE
Stops material	High-alloy steel
Cover material	Wrought aluminum alloy Anodized
Spring pressure piece material	High-alloy steel
Base plate material	Wrought aluminum alloy Anodized
Retaining bracket material	Wrought aluminum alloy Anodized
Cross guide material	Tempered steel
Swivel lever material	Case-hardened steel Burnished
Link material	Case-hardened steel Hardened

<b>Feature</b>	<b>Value</b>
Sensor rail material	Wrought aluminum alloy Anodized
Fixed link material	Wrought aluminum alloy Anodized
Setting screw material	High-alloy steel