

# Mini slide DGSL-16-40-Y3A

Part number: 544000

FESTO



## Data sheet

Feature	Value
Stroke	40 mm
Adjustable end-position range/front length	36.5 mm
Adjustable end-position range/rear length	38.5 mm
Piston diameter	20 mm
Type code	DGSL
Drive unit operating mode	Yoke
Cushioning	Progressive pneumatic shock absorbers at both ends
Mounting position	Any
Guide	Ball bearing cage guide
Structural design	Yoke Piston Piston rod Slide
Position sensing	For proximity sensor
Symbol	00991263
Operating pressure	0.1 MPa ... 0.8 MPa
Operating pressure	1 bar ... 8 bar
Max. speed	0.8 m/s
Repetition accuracy	±0.01 mm
Mode of operation	Double-acting
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	0 - No corrosion stress
Ambient temperature	0 °C ... 60 °C
Impact energy in the end positions	4 J
Cushioning length	14 mm
Max. force F <sub>y</sub>	2527 N
Max. force F <sub>z</sub>	2527 N
Max. torque M <sub>x</sub>	40 Nm
Max. torque M <sub>y</sub>	25 Nm
Max. torque M <sub>z</sub>	25 Nm
Theoretical force at 6 bar, retracting	158 N
Theoretical force at 6 bar, advancing	188 N
Moving mass	486 g
Product weight	1140 g
Alternative connections	See product drawing

<b>Feature</b>	<b>Value</b>
Type of mounting	With through-hole
Pneumatic connection	M5
Note on materials	Free of copper and PTFE RoHS-compliant
Cover material	Wrought aluminum alloy
Seals material	HNBR
Housing material	Wrought aluminum alloy
Piston rod material	High-alloy stainless steel