



Air solenoid valve VZWM-L-M22C-G1-F5-R1

FESTO

Part number: 546166



Data sheet

Feature	Value
Type code	VZWM
Structural design	Diaphragm valve servo-controlled
Actuation type	Electrical
Sealing principle	Soft
Mounting position	Preferably upright
Type of mounting	Line installation
Fitting connection	G1
Electrical connection	Solenoid coil type MH-... , coil can be ordered as an accessory
Nominal width	25 mm
Valve function	2/2, closed, monostable
Flow direction	Non-reversible
Medium	Compressed air as per ISO 8573-1:2010 [7:4:4] Inert gas Water Neutral liquids
Medium pressure of liquid media	0.5 bar ... 6 bar
Medium pressure of gaseous media	0.5 bar ... 10 bar
Differential pressure	0.5 bar
Type of control	Pilot-controlled
Symbol	00995681
Max. viscosity	22 mm ² /s
Temperature of medium	-10 °C ... 60 °C
Temperature of liquid media	5 °C ... 50 °C
Ambient temperature	-10 °C ... 60 °C
Flow rate Kv	10.7 m ³ /h
Standard nominal flow rate	11700 l/min
On switching time	15 ms
Response time "on" for liquid media	300 ms
Switching time off	12 ms
Response time "off" for liquid media	950 ms

Feature	Value
b-value	0.57
C value	41 l/sbar
Note on materials	Contains paint-wetting impairment substances RoHS-compliant
Housing material	Cast stainless steel
Material number of housing	1.4581
Seals material	NBR
Armature tube material	High-alloy steel
Product weight	1100 g
CE marking (see declaration of conformity)	as per EU pressure equipment directive
Corrosion resistance class (CRC)	3 - High corrosion stress
Max. torque for cover screw	30 Nm
Max. tightening torque for connecting thread	350 Nm
Max. tightening torque for coil fastening	2 Nm