



# Air solenoid valve VSVA-B-D52-H-A2-1AC1

Part number: 547097

FESTO



## Data sheet

| Feature                                                                | Value                                                                                 |
|------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
| Valve function                                                         | 5/2, bistable, dominant                                                               |
| Actuation type                                                         | Electrical                                                                            |
| Valve size                                                             | 18 mm                                                                                 |
| Standard nominal flow rate                                             | 550 l/min                                                                             |
| Pneumatic working port                                                 | Sub-base, size 18 mm as per ISO 15407-1<br>Size 02 sub-base as per VDMA 24563<br>G1/8 |
| Operating voltage                                                      | 24V AC                                                                                |
| Operating pressure                                                     | 0.2 MPa ... 1 MPa                                                                     |
| Operating pressure                                                     | 2 bar ... 10 bar                                                                      |
| Structural design                                                      | Piston gate valve                                                                     |
| Degree of protection                                                   | IP65<br>NEMA 4                                                                        |
| Nominal width                                                          | 5 mm                                                                                  |
| Type code                                                              | VSVA                                                                                  |
| Exhaust air function                                                   | With flow control option                                                              |
| Sealing principle                                                      | Soft                                                                                  |
| Mounting position                                                      | Any                                                                                   |
| Conforms to standard                                                   | ISO 15407-1<br>VDMA 24563                                                             |
| Manual override                                                        | Non-detenting                                                                         |
| Type of control                                                        | Pilot-controlled                                                                      |
| Pilot air supply port                                                  | Internal                                                                              |
| Flow direction                                                         | Non-reversible                                                                        |
| Symbol                                                                 | 00991059                                                                              |
| Lap                                                                    | Overlap                                                                               |
| Signal status display                                                  | LED                                                                                   |
| Pilot pressure MPa                                                     | 0.3 MPa ... 1 MPa                                                                     |
| Pilot pressure                                                         | 3 bar ... 10 bar                                                                      |
| Flow rate of pneumatic valve                                           | 750 l/min                                                                             |
| Flow rate of pneumatic valve on individual sub-base                    | 550 l/min                                                                             |
| Optimized flow rate of pneumatic valve pneumatically concatenated flow | 550 l/min                                                                             |
| Changeover time                                                        | 15 ms                                                                                 |
| Duty cycle                                                             | 100%                                                                                  |
| Coil characteristics                                                   | 24 V AC: 50/60 Hz, initial power 3.1 VA, holding power 2.3 VA                         |
| Permissible voltage fluctuations                                       | -15 % / +10 %                                                                         |
| Operating medium                                                       | Compressed air as per ISO 8573-1:2010 [7:4:4]                                         |

| Feature                                   | Value                                                                                |
|-------------------------------------------|--------------------------------------------------------------------------------------|
| Information on operating and pilot media  | Operation with oil lubrication possible (required for further use)                   |
| Vibration resistance                      | Transport application test with severity level 2 as per FN 942017-4 and EN 60068-2-6 |
| Shock resistance                          | Shock test with severity level 2 as per FN 942017-5 and EN 60068-2-27                |
| Corrosion resistance class (CRC)          | 0 - No corrosion stress                                                              |
| Temperature of medium                     | -5 °C ... 50 °C                                                                      |
| Relative air humidity                     | 0 - 90 %                                                                             |
| Noise level                               | 85 dB(A)                                                                             |
| Pilot medium                              | Compressed air as per ISO 8573-1:2010 [7:4:4]                                        |
| Ambient temperature                       | -5 °C ... 50 °C                                                                      |
| Max. tightening torque for valve mounting | 1 Nm                                                                                 |
| Product weight                            | 174 g                                                                                |
| Electrical connection                     | Form C<br>as per DIN EN 175301-803<br>Without PE conductor                           |
| Type of mounting                          | On sub-base                                                                          |
| Auxiliary pilot air port 12               | Sub-base, size 18 mm as per ISO 15407-1                                              |
| Auxiliary pilot air port 14               | Sub-base, size 18 mm as per ISO 15407-1                                              |
| Pilot exhaust air port 82/84              | Not ducted as per standard<br>Ducted                                                 |
| Pneumatic connection 1                    | Sub-base, size 18 mm as per ISO 15407-1                                              |
| Pneumatic connection 2                    | Sub-base, size 18 mm as per ISO 15407-1                                              |
| Pneumatic connection 3                    | Sub-base, size 18 mm as per ISO 15407-1                                              |
| Pneumatic connection 4                    | Sub-base, size 18 mm as per ISO 15407-1                                              |
| Pneumatic connection 5                    | Sub-base, size 18 mm as per ISO 15407-1                                              |
| Pilot interface                           | as per ISO 15218                                                                     |
| Note on materials                         | RoHS-compliant                                                                       |
| Seals material                            | HNBR<br>NBR                                                                          |
| Housing material                          | Die-cast aluminum                                                                    |
| Material of screws                        | Steel<br>Galvanized                                                                  |