


# Compact air cylinder ADNGF-20-25-P-A

Part number: 554224

**FESTO**



## Data sheet

| Feature                                  | Value                                                              |
|------------------------------------------|--------------------------------------------------------------------|
| Stroke                                   | 25 mm                                                              |
| Piston diameter                          | 20 mm                                                              |
| Type code                                | ADNGF                                                              |
| Based on norm                            | ISO 21287                                                          |
| Cushioning                               | Elastic cushioning rings/pads at both ends                         |
| Mounting position                        | Any                                                                |
| Structural design                        | Piston<br>Piston rod<br>Profile barrel                             |
| Position sensing                         | For proximity sensor                                               |
| Protection against torsion/guide         | Guide rod with yoke                                                |
| Operating pressure                       | 0.15 MPa ... 1 MPa                                                 |
| Operating pressure                       | 1.5 bar ... 10 bar                                                 |
| Mode of operation                        | Double-acting                                                      |
| Operating medium                         | Compressed air as per ISO 8573-1:2010 [7:4:4]                      |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC)         | 2 - Moderate corrosion stress                                      |
| LABS conformity                          | VDMA24364-B1/B2-L                                                  |
| Ambient temperature                      | -20 °C ... 80 °C                                                   |
| Impact energy in the end positions       | 0.2 J                                                              |
| Theoretical force at 6 bar, retracting   | 141 N                                                              |
| Theoretical force at 6 bar, advancing    | 188 N                                                              |
| Moving mass at 0 mm stroke               | 60 g                                                               |
| Additional weight per 10 mm stroke       | 26 g                                                               |
| Basic weight with 0 mm stroke            | 161 g                                                              |
| Additional moving mass per 10 mm stroke  | 11 g                                                               |
| Pneumatic connection                     | M5                                                                 |
| Note on materials                        | RoHS-compliant                                                     |
| Cover material                           | Aluminum<br>Anodized                                               |
| Seals material                           | TPE-U(PUR)                                                         |
| Piston rod material                      | High-alloy steel                                                   |
| Material of cylinder barrel              | Wrought aluminum alloy<br>Smooth anodized                          |