


# Air solenoid valve CDVI5.0-MT2H-1X2OLS-EXT

FESTO

Part number: 556380



## Data sheet

Feature	Value
Valve function	2/2, open, monostable
Actuation type	Electrical
Standard nominal flow rate	300 l/min
Pneumatic working port	Sub-base
Operating voltage	24V DC
Operating pressure	-0.9 bar ... 10 bar
Structural design	Piston gate valve
Reset method	Pneumatic spring
Nominal width	5 mm
Type code	CDVI5.0
Exhaust air function	With flow control option
Sealing principle	Soft
Manual override	Non-detenting
Type of control	Pilot-controlled
Pilot air supply port	External
Flow direction	Reversible
Symbol	00992126
Note on forced dynamization	Switching frequency at least once a month
Pilot pressure	3 bar ... 8 bar
b-value	0.34
C value	2.05 l/sbar
Switching time off	14 ms
On switching time	10 ms
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	3 - High corrosion stress
Temperature of medium	-5 °C ... 50 °C
Ambient temperature	-5 °C ... 50 °C
Product weight	185 g
Type of mounting	Screw-in
Pilot exhaust air port 82/84	Sub-base
Pneumatic connection 1	Sub-base
Pneumatic connection 2	Sub-base
Pneumatic connection 3	Sub-base
Pneumatic connection 4	Sub-base
Pneumatic connection 5	Sub-base

<b>Feature</b>	<b>Value</b>
Note on materials	RoHS-compliant
Seals material	NBR TPE-O
Housing material	Die-cast aluminum