

# Swivel actuator unit DSL-32-50-270-P-A-S2-B

Part number: 556510

FESTO



## Data sheet

Feature	Value
Adjustment range of swivel angle	0 deg ... 270 deg
Stroke	50 mm
Piston diameter	32 mm
Swivel angle	0 deg ... 272 deg
Type code	DSL
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position	Any
Precision adjustment	-6 deg
Mode of operation	Double-acting
Structural design	Rotary vane
Position sensing	For proximity sensor
Symbol	00991268
Variants	Through piston rod
Protection against torsion/guide	With plain-bearing guide
Operating pressure	2.5 bar ... 8 bar
Max. impact velocity	0.5 m/s
Max. swivel frequency at 6 bar	2 Hz
Swivel angle backlash	2 deg
Repetition accuracy	1 deg
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-10 °C ... 60 °C
Dynamic load torque	0.8 Nm
Theoretical force at 6 bar, retracting	294 N
Theoretical force at 6 bar, advancing	422.5 N
Theoretical torque at 6 bar	10 Nm
Permissible mass moment of inertia	1.7E-4 kgm <sup>2</sup>
Additional weight per 10 mm stroke	109 g
Basic weight with 0 mm stroke	2840 g
Product weight	2840 g
Type of mounting	Optionally: Clamped in T slot With external thread
Pneumatic connection	G1/8

<b>Feature</b>	<b>Value</b>
Cover material	Wrought aluminum alloy Anodized
Seals material	TPE-U(PU)
Housing material	Wrought aluminum alloy Smooth anodized
Piston rod material	Tempered steel