

Compact air cylinder ADN-1/2"-1/4"-I-P-A

Part number: 557025

FESTO



Data sheet

Feature	Value
Stroke	6.35 mm
Piston diameter	1/2"
Piston rod thread	4-48 UNF-2B
Type code	ADN
Based on norm	ISO 21287
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position	Any
Mode of operation	Double-acting
Piston rod end	Internal thread
Structural design	Piston Piston rod Profile barrel
Position sensing	For proximity sensor
Variants	Piston rod at one end
Operating pressure	0.1 MPa ... 1 MPa
Operating pressure	1 bar ... 10 bar
Operating pressure	14.5 psi ... 145 psi
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Ambient temperature	-20 °C ... 80 °C
Impact energy in the end positions	0.0705 J
Theoretical force at 6 bar, retracting	50.999 N
Theoretical force at 6 bar, advancing	68 N
Moving mass at 0 mm stroke	9.044 g
Additional weight per 10 mm stroke	2.013 g
Basic weight with 0 mm stroke	77.282 g
Additional moving mass per 10 mm stroke	12.049 g
Type of mounting	Optionally: With through-hole With internal thread With accessories
Pneumatic connection	10-32 UNF-2B
Flange screws material	Steel
Cover material	Wrought aluminum alloy Anodized
Material of dynamic seals	TPE-U(PU)

Feature	Value
Piston rod material	High-alloy steel
Material of cylinder barrel	Wrought aluminum alloy Smooth anodized