

# Compact air cylinder ADNGF-1 5/8"-1 1/4"-P-A

Part number: 557246

**FESTO**



## Data sheet

| Feature                                  | Value                                                                        |
|------------------------------------------|------------------------------------------------------------------------------|
| Stroke                                   | 31.75 mm                                                                     |
| Piston diameter                          | 1 5/8"                                                                       |
| Type code                                | ADNGF                                                                        |
| Based on norm                            | ISO 21287                                                                    |
| Cushioning                               | Elastic cushioning rings/pads at both ends                                   |
| Mounting position                        | Any                                                                          |
| Structural design                        | Piston<br>Piston rod<br>Profile barrel                                       |
| Position sensing                         | For proximity sensor                                                         |
| Protection against torsion/guide         | Guide rod with yoke                                                          |
| Operating pressure                       | 0.1 MPa ... 1 MPa                                                            |
| Operating pressure                       | 1 bar ... 10 bar                                                             |
| Mode of operation                        | Double-acting                                                                |
| Operating medium                         | Compressed air as per ISO 8573-1:2010 [7:4:4]                                |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use)           |
| Corrosion resistance class (CRC)         | 2 - Moderate corrosion stress                                                |
| Ambient temperature                      | -20 °C ... 80 °C                                                             |
| Impact energy in the end positions       | 0.6996 J                                                                     |
| Theoretical force at 6 bar, retracting   | 686 N                                                                        |
| Theoretical force at 6 bar, advancing    | 754 N                                                                        |
| Moving mass at 0 mm stroke               | 164.6 g                                                                      |
| Additional weight per 10 mm stroke       | 17.067 g                                                                     |
| Basic weight with 0 mm stroke            | 431.544 g                                                                    |
| Additional moving mass per 10 mm stroke  | 45.162 g                                                                     |
| Type of mounting                         | Optionally:<br>With through-hole<br>With internal thread<br>With accessories |
| Pneumatic connection                     | 1/8 NPT                                                                      |
| Flange screws material                   | Steel                                                                        |
| Cover material                           | Wrought aluminum alloy<br>Anodized                                           |
| Seals material                           | NBR                                                                          |
| Material of dynamic seals                | TPE-U(PU)                                                                    |
| Piston rod material                      | High-alloy steel                                                             |

| Feature                     | Value                                     |
|-----------------------------|-------------------------------------------|
| Material of cylinder barrel | Wrought aluminum alloy<br>Smooth anodized |