


Axial kit EAMM-A-L38-60G

Part number: 557978

FESTO



Data sheet

Feature	Value
Type code	EAMM-A
Mounting position	Any
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	-10 °C ... 60 °C
Transferable torque	4.4 Nm
Product weight	350 g
Interface code, actuator	L38
Interface code, motor in	60G
Note on materials	RoHS-compliant