


# Parallel gripper HGPT-16-A-B-F-G1

Part number: 560196

FESTO



## Data sheet

Feature	Value
Size	16
Stroke per gripper jaw	1.5 mm
Max. interchangeability	≤0.2 mm
Max. gripper jaw angular play ax, ay	≤0.1 deg
Max. gripper jaw backlash Sz	≤0.02 mm
Rotational symmetry	≤0.2 mm
Pneumatic gripper repetition accuracy	≤0.03 mm
Type code	HGPT
Number of gripper jaws	2
Mounting position	Any
Mode of operation	Double-acting
Gripper function	Parallel
Gripping force backup	On opening
Structural design	Inclined plane Positively driven motion sequence
Position sensing	For proximity sensor
Symbol	00995947
Operating pressure	4 bar ... 8 bar
Operating pressure for sealing air	0 bar ... 0.5 bar
Max. operating frequency of pneumatic gripper	≤3 Hz
Min. opening time at 6 bar	19 ms
Min. closing time at 6 bar	30 ms
Max. mass per external gripper finger	40 g
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Degree of protection	IP40
Ambient temperature	5 °C ... 60 °C
Mass moment of inertia	0.163 kgcm <sup>2</sup>
Maximum force on gripper jaw Fz, static	200 N
Maximum torque on gripper jaw, Mx static	10 Nm
Maximum torque on gripper jaw, My static	12 Nm
Maximum torque on gripper jaw, Mz static	6 Nm
Relubrication interval for guidance elements	5 MioCyc
Product weight	100 g

Feature	Value
Type of mounting	Optionally: With internal thread and centering sleeve Via through-hole and centering sleeve With through-hole and dowel pin With internal thread and dowel pin
Sealing air pneumatic connection	M3
Pneumatic connection	M5
Note on materials	Free of copper and PTFE RoHS-compliant
Cover cap material	High-alloy stainless steel
Housing material	Aluminum Anodized
Gripper jaw material	Steel Hardened