



# Mini slide EGSL-BS-35-50-8P

Part number: 562160

FESTO



## Data sheet

Feature	Value
Working stroke	50 mm
Size	35
Run. parallelism along Z-axis	0.02 mm
Parallelism	0.05 mm
Reversing backlash	≤50 μm
Screw diameter	8 mm
Spindle pitch	8 mm/U
Type code	EGSL
Mounting position	Any
Guide	Ball bearing cage guide
Structural design	Electrical mini-slide Guide with ball screw drive
Motor type	Stepper motor Servo motor
Spindle type	Ball screw drive
Symbol	00992069
Position sensing	For proximity sensor
Max. acceleration	25 m/s <sup>2</sup>
Max. speed	0.5 m/s
Repetition accuracy	±0.015 mm
Duty cycle	100%
Corrosion resistance class (CRC)	0 - No corrosion stress
Noise level	60 dB(A)
Degree of protection	IP40
Ambient temperature	0 °C ... 60 °C
Continuous feed force	50 N
Max. driving torque	0.2 Nm
Max. force F <sub>y</sub>	412 N
Max. force F <sub>z</sub>	412 N
Max. torque M <sub>x</sub>	6.2 Nm
Max. torque M <sub>y</sub>	6 Nm
Max. torque M <sub>z</sub>	6 Nm
Max. radial force on actuator shaft	20 N
Max. feed force F <sub>x</sub>	75 N
No-load driving torque	0.015 Nm

Feature	Value
Guide value for payload, horizontal	2 kg
Guide value for payload, vertical	2 kg
Mass moment of inertia JL per kg of payload	0.0162 kgcm <sup>2</sup>
Mass moment of inertia JO	0.0426 kgcm <sup>2</sup>
Feed constant	8 mm/U
Maintenance interval	Life-time lubrication
Moving mass	270 g
Product weight	570 g
Type of mounting	With internal thread With centering sleeve With accessories
Note on materials	Contains paint-wetting impairment substances RoHS-compliant
Cover material	Cast aluminum Painted
Guide rail material	Roller bearing steel
Housing material	Wrought aluminum alloy Anodized
Material of yoke plate	Wrought aluminum alloy Anodized
Spindle nut material	Roller bearing steel
Spindle material	Roller bearing steel