



# Mini slide EGSL-BS-75-300-10P

Part number: 562232

FESTO



## Data sheet

Feature	Value
Working stroke	300 mm
Size	75
Run. parallelism along Z-axis	0.12 mm
Parallelism	0.15 mm
Reversing backlash	≤50 μm
Screw diameter	20 mm
Spindle pitch	10 mm/U
Type code	EGSL
Mounting position	Any
Guide	Ball bearing cage guide
Structural design	Electrical mini-slide Guide with ball screw drive
Motor type	Stepper motor Servo motor
Spindle type	Ball screw drive
Symbol	00992069
Position sensing	For proximity sensor
Max. acceleration	25 m/s <sup>2</sup>
Max. speed	0.65 m/s
Repetition accuracy	±0.015 mm
Duty cycle	100%
Corrosion resistance class (CRC)	0 - No corrosion stress
Noise level	65 dB(A)
Degree of protection	IP40
Ambient temperature	0 °C ... 60 °C
Continuous feed force	300 N
Max. driving torque	3.25 Nm
Max. force F <sub>y</sub>	555 N
Max. force F <sub>z</sub>	555 N
Max. torque M <sub>x</sub>	46.4 Nm
Max. torque M <sub>y</sub>	36.5 Nm
Max. torque M <sub>z</sub>	36.5 Nm
Max. radial force on actuator shaft	300 N
Max. feed force F <sub>x</sub>	450 N
No-load driving torque	0.25 Nm

Feature	Value
Guide value for payload, horizontal	14 kg
Guide value for payload, vertical	14 kg
Mass moment of inertia JL per kg of payload	0.0253 kgcm <sup>2</sup>
Mass moment of inertia JO	1.0667 kgcm <sup>2</sup>
Feed constant	10 mm/U
Maintenance interval	Life-time lubrication
Moving mass	3440 g
Product weight	8050 g
Type of mounting	With internal thread With centering sleeve With accessories
Note on materials	Contains paint-wetting impairment substances RoHS-compliant
Cover material	Cast aluminum Painted
Guide rail material	Roller bearing steel
Housing material	Wrought aluminum alloy Anodized
Material of yoke plate	Wrought aluminum alloy Anodized
Spindle nut material	Roller bearing steel
Spindle material	Roller bearing steel