


# Electric cylinder EGSK-26- -

Part number: 562751

FESTO



## Data sheet

Overall data sheet – Individual values depend upon your configuration.

Feature	Value
Working stroke	50 mm ... 200 mm
Size	26
Screw diameter	8 mm
Type code	EGSK
Mounting position	Any
Guide	Recirculating ball bearing guide
Structural design	Electromechanical linear axis with ball screw drive
Homing	Reference switch
Spindle type	Ball screw drive
Symbol	00991211
Max. acceleration	10 m/s <sup>2</sup>
Max. speed	0.28 m/s ... 0.83 m/s
Repetition accuracy	±0.003 - ±0.01 mm
Corrosion resistance class (CRC)	0 - No corrosion stress
Degree of protection	IP10
Ambient temperature	0 °C ... 40 °C
Fixed bearing dynamic basic load rating	1380 N
Linear guide dynamic basic load rating	5746 N
2nd moment of area ly	17000 mm <sup>4</sup>
2nd moment of area lz	150000 mm <sup>4</sup>
Max. feed force Fx	116 N ... 184 N
Linear guide statistical basic load rating	12150 N
Mass moment of inertia JH per meter of stroke	0.0316 kgcm <sup>2</sup>
Feed constant	2 mm/U ... 6 mm/U
Statistical fixed bearing load rating	1760 N
Type of mounting	With internal thread and dowel pin
Material of end caps	Die-cast aluminum Coated
Profile material	High-alloy stainless steel
Note on materials	Contains paint-wetting impairment substances RoHS-compliant
Drive cover material	Die-cast aluminum Coated
Slide material	Steel
Spindle nut material	Steel

Feature	Value
Spindle material	Steel