


Pressure regulator MS12-LR-G-PE6

Part number: 564888

FESTO



Data sheet

Feature	Value
Size	12
Type code	MS12
Series	MS
Mounting position	Any
Structural design	Pilot-controlled diaphragm regulator
Controller function	Outlet pressure constant With primary pressure compensation With secondary exhausting With return flow function
Symbol	00991856
Pressure gauge	with pressure gauge
Operating pressure	1.15 bar ... 8 bar
Pressure regulation range	0.15 bar ... 6 bar
Max. pressure hysteresis	0.04 bar
Flow rate of secondary venting	≤600 l/min
Standard nominal flow rate	12000 l/min ... 21000 l/min
DC operating voltage range	21.6 V ... 26.4 V
Max. electrical power consumption	3.6 W
Max. current consumption	0.15 A
Nominal operating voltage DC	24 V
Residual ripple	10 %
Analog input signal range	0 - 10 V
KC characters	KC EMC
CE marking (see declaration of conformity)	As per EU EMC directive
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4] Inert gas
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Storage temperature	-10 °C ... 60 °C
Temperature of medium	10 °C ... 50 °C
Degree of protection	IP65
Ambient temperature	10 °C ... 50 °C
Product weight	4000 g
Type of mounting	Optionally: Line installation With mounting bracket
Pneumatic connection 1	Sub-base
Pneumatic connection 2	Sub-base

Feature	Value
Covering material	PA
Note on materials	RoHS-compliant
Lower cover material	Wrought aluminum alloy
Seals material	NBR
Material of spring	Spring steel
Housing material	Die-cast aluminum
Diaphragm material	NBR
Valve tappet material	Wrought aluminum alloy NBR High-alloy stainless steel